

MONTAGEANLEITUNG

 MONTAGEANLEITUNG
 ASSEMBLY INSTRUCTION
 DE INSTRUCTIE VAN DE ASSEMBLAGE
 ISTRUZIONE DELL'ASSEMBLEA
 INSTRUCCIÓN DE ASAMBLEA
 INSTRUCTION DE MONTAGE
 NÁVOD K MONTÁŽI
 MONTERINGSANVISNING

 MONTAJ TALIMATI
 ASENNUSOHJE
 BRUGSANVISNING
 BRUKSANVISNING
 UPUTE ZA MONTÁŽU
 NAVODILA ZA MONTAŽO
 SZERELÉSI ÚTMUTATÓ
 INSTRUCTIUNI DE MONTAJ



Modell-Nr.

12120

Friedrich Küpper GmbH
 Friedrich-Küpper-Weg
 54570 Berlingen
 Deutschland

Telefon +49 (0) 65 91 - 95 42 0
 Telefax +49 (0) 65 91 - 95 42 17
 E-Mail info@friedrich-kuepper-gmbh.de
 Internet www.friedrich-kuepper-gmbh.de

ART.-NR. FRONT KORPUS

12121 Grün Silber

12122 Rot (ähnl. RAL 3002) Silber

12124 Blau Silber

12127 Ultramarinblau (RAL 5002) Silber

12126 Silber Schwarz

LIEFERUMFANG / SCOPE OF SUPPLY

EINZELTEILE / PIECES

A

1x

772 mm x 475 mm



C

1x

1057 mm x 473 mm



B

1x

772 mm x 475 mm



D

1x

1057 mm x 473 mm



F

1x

505 mm x 450 mm



E

1x

985 mm x 480 mm



H

6x

450 mm x 445 mm



Y

1x


1200 mm x 600 mm



I

6x


470 mm x 130 mm



J

6x

450 mm x 120 mm



X

7x

450 mm x 20 mm



M

1x

980 mm x 130 mm



Q

1x


955 mm x 420 mm



BEUTELINHALT / BAG CONTENT



BENÖTIGTES WERKZEUG / NEEDED TOOLS




1.




2. WICHTIG / IMPORTANT



3.  2x M5  2x M5 x 10  2x 5,3 MM




4.




5.  2x M5  2x M5 x 10  2x 5,3 MM  2 SW 8  1 PH 2 X 100



6.




7.



ZU SCHRITT 3. / IN ADDITION TO STEP 3.


②  SW 8 ①  PH 2x100




8. WICHTIG / IMPORTANT




9. WICHTIG / IMPORTANT



10.  6x M5  6x M5x10  6x 5,3 MM ②  SW 8 ①  PH 2x100




11.  6x M5  6x M5x10  6x 5,3 MM ②  SW 8 ①  PH 2x100



12. 4x M8 4x 4x


5



13. 6x CR




14. 6x CL




15. 12x M4 12x M4 x 10

2 SW7 1 PH1 x 100




16. 36x M4 36x M4 x 10


② SW7 ① PH1x100




17.



18.



19.



20.

12x KU 4 x 16

6x



①

PH 2 x 100



21.



22.




23.



24.



25.



26.

4x KU 4x16

2x




①


PH 2x100



27.



28.



29.



30.





Modell-Nr.

12120